



TECHNICAL DATA:			ACCESSORIES:					INSTALLATION:					
OPERATING VOLTAGE 210KV DC 1. TERMINAL MATERIAL BRASS 2. CONTACT CAVITY & TAPER MUST NOT BE FILLED WITH ANY PETROLIUM BASED OIL. 3. MATERIAL OF INSULATION IS CAPABLE OF CONTINUOUS IMMERSION IN SHELL DIALA B.G. OIL OR EQUIVALENT.			CABLE ASSEMBLY USED WITH THIS RECEPTACLE TO HAVE 210KV SEIFERT TERMINATION.					WARNING: THIS SOCKET MUST ONLY BE FITTED BY A TRAINED PERSON SEE CABLE TERMINATION DATA SHEET DS 1005 OR DS1006 FOR FITTING OF CABLE TERMINATION TO RECEPTACLE.					
<div>ESSEX</div> <p>Dandong Light Electric Co.,Ltd Rm.1606 Jiadi Square,No.64,Binjiang Middle Rd, Zhenxing, Dandong, Liaoning China T:0415-6123232 F:0415-6123533</p>			REVISIONS			DUE TO CONTINUING PRODUCT DEVELOPMENT ESSEX X-RAY RESERVES THE RIGHT TO MODIFY DATA WITHOUT NOTICE							
			NO.	DATE	BY	DRAWN	APPROVED	DATE	ISSUE	SCALE	© NOT TO BE REPRODUCED IN WHOLE OR PART WITHOUT PRIOR PERMISSION OF ESSEX X-RAY & MEDICAL EQUIPMENT LTD.		
			2	15.07.99	DCN 1049	JDF		15.07.96	4	N.T.S.			
			3	11.05.01	DCN 1455	TITLE 210KV SEIFERT (R30) TUBE RECEPTACLE ESSEX PART NO. S61007						DRAWING No. DS1013	
			4	01.03.04	DCN 2000								