
100KV (R10) NOMINAL OPERATING VOLTAGE 100KV DC PART No. A92001 DRAWING GAI197



A

THIS DATA SHEET IS FOR IDENTIFICATION PURPOSES ONLY. NOMINAL DIMENSIONS IN MM.

TECHNICAL DATA:				ACCESSORIES:						INSTALLATION:		
TERMINATION:— NOMINAL OPERATING VOLTAGES USING AN ESSEX X—RAY APPROVED RECEPTACLE			CLAMPING SLEEVES:— FOR CLAMPING SLEEVE OPTIONS SEE DATA SHEETS DS1060, DS1061, DS1062, DS1063, DS1064 INSTALLATION GREASE P00075						BLANKIN OIL MUS HIGH VO ENSURE TERMINA GAP BE AND SO	WARNING: BLANKING PLUGS SHOULD ONLY BE FITTED BY A TRAINED PERSON. OIL MUST NOT BE USED ON THE RUBBER TERMINATION, ONLY SUITABLE HIGH VOLTAGE GREASE. ENSURE BY ADJUSTING THE CLAMPING SLEEVE THAT WHEN THE TERMINATION IS FULLY INSERTED IN THE SOCKET THERE IS A SUITABLE GAP BETWEEN THE MATING FACES OF THE CLAMPING SLEEVE AND SOCKET BEFORE TIGHTENING THE CLAMPING SLEEVE. SEE DATA SHEETS DS1041, DS1043, DS1044.		
Dandong Light Electric Co.,Ltd Rm.1606 Jiadi Square,No.64,Binjiang Middle Rd, Zhenxing, Dandong, Liaoning China T:0415-6123232 F:0415-6123533		REVISION	IS	DUE TO CONTINUING PRODUCT DEVELOPMENT ESSEX					X-RAY	RESERVES THE RIGHT TO MODIFY	DATA WITHOUT NOTICE	
	NO. 2	DATE 26.04.10	BY DCN 3075	DRAWN MGM	APPROVED	DATE ISSUE 12.11.04		SCALE	NTS	NOT TO BE REPRODUCED IN WHOLE OR PART WITHOUT PRIOR PERMISSION OF ESSEX X-RAY & MEDICAL EQUIPMENT LTD.		
				TITLE		В	BLANKING PLI		UGS		DRAWING No.	